Form-Fit Liners

Form-fit (cube-shaped) liners are manufactured to form fit the internal shape of your intermediate bulk container. Form-fit IBC liners provide high performance in critical applications, such as top-fill applications using a bridge or automated filler; containers with no access doors for placing



a liner at the bottom; high speed fills and viscous products that would get caught in the folds of pillowshaped liners.

Benefits

- Manufactured in a clean environment, using cutting-edge CDF1 Smart Seal Technology[™] that monitors and ensures consistent, high quality seals
- Ideal for both returnable type containers and one-way disposable corrugated containers
- Ensures the absolute purity of your product
- Easy to fill, using either top or bottom fill applications
- Designed to accommodate high-speed fills; the auto unfold feature minimizes bag handling during a fill
- Squared bottom eliminates the need for a cassette in many cases
- No pockets or folds trapping residual product while emptying
- CDF offers a variety of films, fitments and fitment placements



Form-Fit Liners

CDF1 Smart Seal Technology™

Using state of the art equipment and quality control standards of the highest caliber, CDF1 Smart Seal Technology ensures the ultimate reliability of IBC form-fit liners. Proprietary CDF1 Smart Seal Technology optimizes precision and consistency through monitoring the temperature, time and pressure of every seal on every liner.

Multiple Sizes

Form-fit liners are available for all intermediate bulk container sizes.

Multiple Fitment Choices

CDF fitments are available in a variety of sizes.

Material Choices

All liners are made in America. The inside layer is made from FDA-approved films.

EVOH film is widely used in the food packaging industry. It is a strong, flexible, transparent, film with good moisture and excellent oxygen barrier specifications.

Flexus[™] and Flexus HF metallocene LLDPE are for general use and provide durability and flex crack resistance.

Tenalon™ co-extruded nylon film provides abrasion resistance, durability and strength.



The film materials used in the manufacture of our IBC liners comply with FDA Regulations 21 CFR 177.1520, CFR 175.105, 177.1390 and CFR 177.1630.

We guarantee that our liners will be constructed from the specified materials and that CDF will not knowingly use materials that are out of specification or could be adulterated. No additives are introduced during the heat-sealing process.

Custom Designs

CDF will always consider custom designs.

Most Popular Product

- **7-5548**
- **7-5342**



CDF warrants that its products will be free from defects in material and workmanship for one-hundred eighty (180) days after the date of delivery. Warranty claims must be made in writing no later than five (5) business days after the expiration of the warranty period. CDF's obligations under this warranty are limited solely to replacement of such products as are proven to be defective after CDF's inspection. Prior to use, the user shall independently determine the suitability of the products for the user's intended use and user assumes all risk and liability whatsoever in connection therewith. CDF products are intended for single use application. Any reuse of the liner and/or fitment voids this warranty.

CDF EXPRESSLY DISCLAIMS AND EXCLUDES ANY AND ALL WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE RELATING TO THE USE OR PERFORMANCE OF CDF PRODUCTS. CDF SHALL NOT BE LIABLE FOR PERSONAL INJURY OR PROPERTY DAMAGE UNLESS CAUSED SOLELY BY CDF'S NEGLIGENCE. CDF SHALL NOT BE LIABLE FOR LOSS OF PROFIT OR OTHER SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF CDF PRODUCTS, REGARDLESS OF THE LEGAL THEORY ON WHICH THE CLAIM IS BASED AND EVEN IF CDF HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

